

The operating status conditions of the printer and the amounts of inks usedcan be monitored remotely. PICT allows you to do other work during printing, helping you to perform operations in a planned manner.

You can also schedule maintenance and preparation for ink refilling in advance.



Expand capability in the combination with our cutting machines and expand its potential.

You can select an appropriate one from 4 sizes in line-up for space and application choice.

1,200mn

Wide range of size and head types are available, as well as customization. We can also customize the machines. Please contact local Mimaki sales office or dealers for more details



1,200mm







CF2 series

■Specifications

ltem -		Specifications	
		JFX200-1213 EX	
Head		On-demand piezo head (3 staggered print heads)	
Print resolution		300 dpi, 450 dpi, 600 dpi, 900 dpi, 1,200 dpi	
	Type/Color	Rigid UV curable ink LH-100	
		Flexible UV curable ink LUS-120 / LUS-150 / LUS-211 / LUS-350	
	Capacity*1	1 L bottle / 250 ml bottle	
	Ink circulation system*2	White ink circulation by MCT (Mimaki Circulation Technology)	
Max. Printable area (W x D)		1,270 mm × 1,300 mm	
H	Size (W × D)	1,270 mm × 1,300 mm	
	Height	50 mm (2.0") or lower	
	Weight	50 kg/sqm (110.2 lb/sq. ft2) or less (non concentrated load)	
Media suction Suction areas		Vacuum suction + foot switch	
		2 partition (X direction)	
UV method		LED-UV	
Interface		USB, Ethernet	
Applicable standards		VCCI class A, CE mark, CB report, U.S. safety standard UL (UL62368-1), RoHS Directive, FCC Class A, Machinery Directive, EAC, RCM	
Power		Single-phase AC200 to 240 V, 50/60 Hz, 12 A or lower	
Power consumption		2.88 kVA	
Operating environment		15 - 30 degC (59 - 86 degF)	
	Humidity	35 - 65 %Rh	
	Optimal temperature	20 - 25 degC (68 - 77 degF)	
	Temperature gradient	Less than ± 10 degC / h (± 18F/h)	
	Dust	Equivalent to an office	
Assembled dimensions (W×D×H)		3,142 mm x 2,320 mm x 1,235 mm	
Weight		550 kg	

■Optional Accessories

Item No.	Item	Remarks	
OPT-J0348	Optional blower Connector Kit	Necessary kit for connecting an optional vacuum unit	
OPT-J0216	Vacuum unit (φ3 mm × 200 mm (φ 0.1 in. × 7.9 in.))	Three-phase, 200 V-240 V, 30 A, 3.4 kW	
OPT-J0217	Vacuum unit (φ1 mm × 200 mm (φ 0.04 in. × 7.9 in.))	Single-phase, 200 V-240 V, 30 A, 1.9 kW	
OPT-J0232	Vacuum unit (φ3 mm × 400 mm (φ 0.1 in. × 15.7 in.))	Three-phase, 380 V-480 V, 20 A, 3.4 kW	
OPT-J0499	4C+4White ink applying kit	Necessary kit for 4C+4White ink set	
OPT-J0513	Lift-Up Block		
OPT-J0569	lonizer kit		

■Supplies

	Color	Item No.	Remarks
LH-100	Cyan	LH100-C-BA	
	Magenta	LH100-M-BA	
	Yellow	LH100-C-BA	
	Black	LH100-K-BA	
	Light cyan	LH100-LC-BA	
	Light magenta	LH100-LM-BA	
	White	LH100-W-BA	
	Clear	LH100-CL-BA	
LUS-120	Cyan	LUS12-C-BA	
	Magenta	LUS12-M-BA	Ink package:
	Yellow	LUS12-Y-BA	
	Black	LUS12-K-BA	
	White	LUS12-W-BA	
	Clear	LUS12-CL-BA	
LUS-150	Cyan	LUS15-C-BA	
	Magenta	LUS15-M-BA	
	Yellow	LUS15-Y-BA	
	Black	LUS15-K-BA	
	Light cyan	LUS15-LC-BA	
	Light magenta	LUS15-LM-BA	
	White	LUS15-W-BA	
LUS-350	Cyan	LUS35-C-BA	
	Magenta	LUS35-M-BA	
	Yellow	LUS35-Y-BA	
	Black	LUS35-K-BA]
	White	LUS35-W-BA	
	Clear	LUS35-CL-BA	
Primer*3	PR-200	PR200-Z-BA	
Tungsten repla	acement needle for ionizer	SPA-0208	4pcs.

- *1: LH-100, LUS-120 and PR-200 come in both 250 ml and 1 L bottles
- *3: The PR-200 is not compatible with LUS-211 and LUS-350.
- * As the stretchability of flexible ink may vary depending on materials please have a prior test print.
- * LH-100, LUS-120 and LUS-150 are GREENGUARD Gold certified ink.

- *Please use Category 6 (CAT6) network cables. *Cannot be connected through the router
- *When printing from ethernet, place the printer and output PC on the same network. *When using a switching hub, a 1000BASE-T compatible hub is necessary.
- *Although up to 4 printers can be registered with RasterLink7, printing may stop

depending on the network environment.



·As physical properties of ink (adhesion, weather resistance etc.) are different depending on media, please be sure

⚠ Safety notice:

This product is equipped with UV irradiation equipme

Please pay attention to the following notes in order to use safely.

Do not look directly into the UV light source nor place your hand, or expose your skin directly to the UV light source.
Depending upon print mode, some VOC emittance from printed parts not yet cured and hardened may occur.
In addition, please be sure to read and follow the instructions and guidelines of the manual carefully.

Exclusively Distributed by:



MAKATI (HEAD OFFICE)

8837 Sampaloc St., San Antonio Vilage,

Makati City 1203

Contact Nos.: 896-6698 / 890-2657 / 551-2162

163 Sikatuna corner Jakosalem St., Brgy., Zapatera Cebu City Contact No.: (032) 412-5661

CAGAYAN DE ORO

Goking Bldg., San Pedro St., Gusa, Cagayan De Oro Contact No.: (088) 885 0410

PANGASINAN

Bypass Road Brgy. Sto Domingo Urdaneta City, Pangasinan Contact No.: (075) 529-2367

DAVAO

Bajada, Davao City Contact No.: (082) 221-0921

Dasi Compound Water District,

f /BigPixGraphicSystemsInc

INDUSTRIAL PRODUCTS

LED-UV Curing Flatbed Inkjet Printer



JFX200-1213 EX



Single unit, various applications.





















01 / Middle-size flatbed (up to 1270 mm imes 1300 mm)

Single unit - sign graphics & paper package print capability

30% less than JFX200-2513EX body size.

Even table size supports all the international A size.

O Sign graphics use supports A0 size sign panel

• Paper and package supports standard coated cardboard size.


1,270mm A1 A2



02 / max. 25ml/h $\,$ **The highest-in-class productivity**

Suitable as an upgrade from a desktop UV printer

• Print speed comparison between the JFX200-1213EX and the UJF-6042MkIlle



$\left. 03 \right/$ Even faster texture printing

Fast, attractive and easy, added value texture printing

Increased braille printing spee. 2 types expression capability for application

All of these can be done just with standard design software and RasterLink7. Bring texture design into shape instantly.

High-speed Braille printing that is only possible with Mimaki's flatbed technology




2.5D print that combines texture print and smoother bumps and dips

Vacuum valve

Ink tanks

(pull-out unit)









Automatically generates texture layering data based on graphic data in RasterLink7.

tha layers are, highlights bumpes and dips.

High image quality printing

Mimaki's advanced imaging technology realizes smooth gradation and high density print.

Fast and high quality production for custom goods, and signage.

Three different ink dot sizes are used in

printing to enable high-quality prints with

Variable dots

reduced graininess.

(Fixed Dot Image)

Waveform control

By discharging spherical ink droplets directly, depositing of droplets is facilitated and overlapping between dots is reduced, achieving a sharp print quality with low grain.

JFX200-1213 EX

(Non-spherical discharge)



(Discharged in a nearly true spherical state)

the edges are blurred

High precision landing is possible

Sharp finish with little grain.

Control panel

Carriage

(Variable Dot Image)








Dots are combined including the minimum size of 5 pl to enable grainless, smooth color printing.


MAPS (Mimaki Advanced Pass System)

Banding (horizontal stripes), uneven color, or glossy streak can be reduced to produce smooth prints by printing pass boundaries fading in gradation.

(Without MAPS (Image))



(With MAPS (Image))



Based on printing conditions such as media/ink type and resolution, the most suitable gradation pattern is automatically selected and printed.

the based graphic design High-speed mode

braille dots don't interrupt

Standard mode Braille part is constructed by clear ink emboss printing, Transparent

High-speed texture printing by bi-directional printing, utilised for braille and pictograms.





Layers UV ink to make bumpy expressions, the thicker

Operator-friendly user interfaces easily accessible from the front

V2 525_{mm} 775_{mm} V1

Valve and foot switch for vacuum control

The vacuum area is divided into a front section and a rear section. The valve can be used to switch between them easily depending on the media size. The foot switch allows you to turn vacuum on/off while checking the media location






Olnk tank unit

The ink bottles can be accessed from the front side of the printer for replacement and maintenance. This minimizes the pathway to be followed

by operators increasing work efficiency



Mimaki's technology for realizing stable operation



Auto maintenance function to shorten downtime

